

Electric Furnace for determining the amount of soot and filler

- Featured PID control system with digital display for easy application setup for easy test setting
- Equipped with cast masses of different dimensions with Swedish Kanthal wire material with long service life and temperature uniformity inside the furnace
- With capability of increasing the temperature up to 1200 ° C , and thermocouple type k with a precision of 1 ° C
- Equipped with accessories such as glass equipment, nitrogen capsules, flow meter, and chemicals appropriate to the type of test
- Performing test in accordance with the standards ISO 6964, ISO 3451, ASTM D1603

